

LQW2UAS18NJ0C#

Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.

Please download the latest datasheet of LQW2UAS18NJ0C# from the official website of Murata

"#"at the end indicates the package specification code.

Air-core inductor with non-magnetic electrode material which does not disturb magnetic field in magnetic field utilized application such as MRI.













< List of part numbers with package codes > LQW2UAS18NJ0CB LQW2UAS18NJ0CL





Applications

Please be sure to read and comply with
these "Precautions for use."
Consumer equipment,Medical
equipment [GHTF A/B/C] except for
implant & surgery & auto injector,
Industrial equipment except for
transportation & facility & energy
equipment
Please refer to Our Website and
specifications, etc. for information about
the performance, functions, quality,
management, and safety required for
the above applications, and use
Products after confirming the
performance and reliability of the actual
Product.
Canalimar aguinment
Consumer equipment



Appearance & Shape





1 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





LQW2UAS18NJ0C#

Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.

Please download the latest datasheet of LQW2UAS18NJ0C# from the official website of Murata

http://www.murata.com/en/products/productdetail?partno=LQW2UAS18NJ0C%23

"#"at the end indicates the package specification code.



References

Packaging	Specifications	Standard Packing
		Quantity
В	Bulk(Bag)	500
L	180Embossed Tape	2000

I	Mass (typ.)	
-	1 piece	0.039g

2 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





LQW2UAS18NJ0C#

Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.

Please download the latest datasheet of LQW2UAS18NJ0C# from the official website of Murata

http://www.murata.com/en/products/productdetail?partno=LQW2UAS18NJ0C%23

"#"at the end indicates the package specification code.



Specifications

L size	2.62±0.3mm
W size	2.45±0.2mm
T size	1.83±0.2mm
Size code inch (mm)	1008 (2520)
Inductance	18nH±5%
Inductance Test Frequency	50MHz
Rated current (Itemp) (Based on Temperature rise)	1000mA
Max. of DC resistance	0.11Ω
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 85°C
Class of magnetic shield	Non-Shielded
Q(min.)	50
Q Test Frequency	350MHz
Self resonance frequency (min.)	2500MHz
Brand	Murata
Series	LQW2UAS_0C

3 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



information provided may not be the most current.

Please download the latest datasheet of LQW2UAS18NJ0C# from the official website of Murata

http://www.murata.com/on/organicate/organicate/organicate/on/organicate/organ

LQW2UAS18NJ0C#


"#"at the end indicates the package specification code.


Note: If you have not downloaded this document from our official website, please note that the




Characteristic Data

The charts below may show another part number which shares its characteristics.







4 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

 $2. This \ data{sheet has only typical specifications because there is no \ space for \ detailed \ specifications.}$

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

